

H05 Lite

Thank you for purchasing this Olight Product. Please read this manual carefully before use and keep it for future reference!



DANGER

- DO NOT shine the light directly into human eyes. This may cause temporary blindness, or permanent damage to the eyes.

WARNING

- Please ensure that the batteries are inserted following the direction of the positive (+) and negative (-) marks.
- DO NOT power on the headlamp by mixing used and new batteries or batteries of different brands together.
- DO NOT let children wear or use the headlamp unless accompanied by a parent or legal guardian.


NOTICE

- When using alkaline or carbon batteries, please replace the batteries once they are drained, to avoid potential battery leakage.
- Before long-term storage, please take out the batteries from the light to avoid battery leakage.
- The headlamp is IPX2 water-resistant. Please DO NOT expose it to the rain.
- Please store the headlamp in a dry environment to extend its service life.

IN THE BOX




H05 Lite
(Including the headlamp strap)



AAA Alkaline Batteries
(Installed inside the headlamp)


PRODUCT OVERVIEW



Button
Battery Compartment Key
Optical Lens

AVAILABLE BATTERIES

- 2 x AAA Alkaline Battery (included)
- 2 x AAA Carbon Battery (compatible)
- 2 x AAA Lithium-ion Battery (compatible)



	7m	14cd	IPX2	1m
	58.3*36.5*33.8mm (Headlamp)	66.5g / 2.35oz		2.30*1.44*1.33in (Headlamp)

(Including headlamp strap)

* All above specifications are test results based on ANSI/NEMA FL1-2009 Standards. The tests are performed using two AAA Alkaline batteries included with the product.

SPECIFICATIONS

- 2 x AAA Alkaline Battery (included)
- 2 x AAA Carbon Battery (compatible)
- 2 x AAA Lithium-ion Battery (compatible)

HIGH

45

lumens

100%

10min

56%

140min

MEDIUM

20

lumens

100%

4h

LOW

5

lumens

100%

10h

HIGH

45

lumens

100%

10min

56%

140min

MEDIUM

20

lumens

100%

4h

LOW

5

lumens

100%

10h

HIGH

45

lumens

100%

10min

56%

140min

MEDIUM

20

lumens

100%

4h

LOW

5

lumens

100%

10h

HIGH

45

lumens

100%

10min

56%

140min

MEDIUM

20

lumens

100%

4h

LOW

5

lumens

100%

10h

HIGH

45

lumens

100%

10min

56%

140min

MEDIUM

20

lumens

100%

4h

LOW

5

lumens

100%

10h

HIGH

45

lumens

100%

10min

56%

140min

MEDIUM

20

lumens

100%

4h

LOW

5

lumens

100%

10h

HIGH

45

lumens

100%

10min

56%

140min

MEDIUM

20

lumens

100%

4h

LOW

5

lumens

100%

10h

HIGH

45

lumens

100%

10min

56%

140min

MEDIUM

20

lumens

100%

4h

LOW

5

lumens

100%

10h

HIGH

45

lumens

100%

10min

56%

140min

MEDIUM

20

lumens

100%

4h

LOW

5

lumens

100%

10h

HIGH

45

lumens

100%

10min

56%

140min

MEDIUM

20

lumens

100%

4h

LOW